



Pass and Seymour

Discontinued - Nylon Strain Relief Cord Grip, 3/4-in NPT 90-Degree, .500-.625 OD Range, Stainless Steel Mesh
Part No. CGN7590500M

Non-Metallic Cord Connectors are constructed of a durable, nylon material which offers excellent corrosion resistance, is lightweight, durable and ideal for use in damp environments. Nylon Cord Connectors are ideally suited for use in applications with moisture or washdowns and they provide an environmental seal against dirt, coolants, as well as other chemicals.



Features & Benefits

Heavy duty Nylon body is resistant to impact and corrosion

Rubber grommet provides a liquid-tight seal and reduces cord pull-out while resisting chemicals

Available in straight, 90°, and underground feed styles

Color coded grommets make for easy identification and ease of installation

Rugged construction suitable for various industrial applications such as MRO, food processing, water/waste water, marine, pulp & paper, and petrochemical

Specifications

General Info

| | | | |
|--------------------|------------------------|--------------|-----------------|
| Product Line | Pass & Seymour | UPC Number | 785007057805 |
| Country Of Origin | Mexico | Construction | Nylon Cord Grip |
| Application Sector | Commercial, Industrial | Standard | UL Listed |

Listing Agencies / 3rd Party Agencies

| | |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

Technical Information

| | | | |
|---------------------|--------|---------------------|----------|
| Maximum Cable Range | 0.5 in | Minimum Cable Range | 0.625 in |
|---------------------|--------|---------------------|----------|