Pass and Seymour
**Hard Use Specification Grade Switch, White**
Part No. CSB20AC1W



Construction 1-Pole Switch, Back and Side-Wire, 20A 120/277V.

## Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

One-piece steel strap with integral ground is plated for corrosion resistance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Heavy-duty toggle bumpers for smooth and quiet operation.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Oversized silver alloy contacts for longer dependable switch life.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL 498/20 | | |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.32 in | Product Depth US | 1.073 in |

| | |
|---|---|
| Product Height US | 3.281 in |

## Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | 140597 | cULus Listed | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Actuator | Toggle | Contact Rating | 120/277Vac, 20Amp |
| Amperage | 20 A | Action | Single pole |
| Number of Poles | Single Pole | Voltage | 120 V |