



Ortronics

Infinium Ultra M4 Cassette - 24 Fiber - LC Duplex to MPOM - OM4 - Universal Polarity

Part No. LM4-LC24H-3C3UN

Infinium M4 Cassettes are part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution can enable industry leading pre-terminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

## Features & Benefits

LC adapter with internal shutter: Ensures eye safety by blocking laser light when the connector is removed. Automatic shutter requires no manual handling. Compatible with LC connectors, keeps the interior clean, and allows visible light to pass through.

Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber

Base 8 Connectivity Benefits: Optimized for 8-fiber transceivers and technologies, ensures 100% fiber utilization, matches common port counts on network devices, and offers flexibility for easy migration to 40G/100G/400G networks.

## Specifications

### General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875031161	Country Of Origin	Mexico
Features	Keyed Connector	Application Sector	Commercial
Standard	TIA-568-C.3	Warranty Type	5-Year
Type	Cassette		

### Dimensions

Product Width US	4.24 in	Product Depth US	4.77 in
Product Height US	1.14 in		

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

---

Fiber Optic Cable Type	OM4	Compatibility	HDFP, LM4
Number of Ports	24	Simplex/Duplex	Duplex
Single/Multimode	Multimode	Performance Level/Tier	Infinium Ultra

---