



Ortronics
Infinium Ultra M4 Cassette - 24 Fiber - LC Duplex to MPOM - OS2 - Universal Polarity
Part No. LM4-LC24J-3C2UN



Infinium M4 Cassettes are part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution can enable industry leading pre-terminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

LC adapter with internal shutter: Ensures eye safety by blocking laser light when the connector is removed. Automatic shutter requires no manual handling. Compatible with LC connectors, keeps the interior clean, and allows visible light to pass through.

Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber

Base 8 Connectivity Benefits: Optimized for 8-fiber transceivers and technologies, ensures 100% fiber utilization, matches common port counts on network devices, and offers flexibility for easy migration to 40G/100G/400G networks.

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875032373	Country Of Origin	Mexico
Features	Keyed Connector	Application Sector	Commercial
Standard	TIA-568-C.3	Warranty Type	5-Year
Type	Cassette		

Dimensions

Product Width US	4.24 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Compatibility	HDFP, LM4
------------------------	-----	---------------	-----------

Number of Ports	24	Simplex/Duplex	Duplex
-----------------	----	----------------	--------

Single/Multimode	Single-Mode	Performance Level/Tier	Infinium Ultra
------------------	-------------	------------------------	----------------
