




Wattstopper
Discontinued - DLM Pre-Engraved Wall Switch, 3-Button w/IR, ON/OFF w/Arrows, Lt. Almond
Part No. LMSW-103-LA-ENG2



LMSW-100 Series Digital Wall Switches are low voltage devices for energy-saving manual on/ off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

Features & Benefits

2-Button Wall Switch

LMSW-100 Series Digital Wall Switches are low voltage devices for energy-saving manual on/ off control of one or more loads from one or more locations

They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room Low voltage pushbutton switches for control of multiple loads controllers

Each button can control individual or multiple loads, or one Plug to other components using Cat 5e cable and RJ45 connectors eliminating wiring errors

Customizable buttons with LED status indicators

IR transceiver for wireless configuration and remote control

Plug n' Go automatic configuration and Push n' Learn for personalization

Specifications

General Info

| | | | |
|--------------------|-------------|--------------------|----------------------------|
| Product Line | Wattstopper | Color | Light Almond |
| Finish | Glossy | UPC Number | 754182947171 |
| Country Of Origin | China | Product Series | LMSW |
| Switch Type | Push | Number of Switches | 3 |
| Application Sector | Commercial | Standard | UL, cUL, FCC part 15, RoHS |
| Warranty Type | 5-Year | Type | Switch |

Dimensions

| | | | |
|-------------------|--------------|-------------------|-----------|
| Product Width US | 1.8 in | Product Weight US | 0.1861 lb |
| Product Volume US | 19.845 cu in | Product Depth US | 1.6 in |
| Product Height US | 4.2 in | | |

Technical Information

| | | | |
|---------------------------|---------------------------|---------------------------|---------------------------|
| Operating Temperature Min | 0 °C | Compatibility | DLM Wired |
| Has Battery | No | Operating Temperature Max | 55 °C |
| Number of Buttons | 3 | Number of Rockers | 0 |
| Topology | Free Topology | Input Voltage | 24 VDC |
| Indoor/Outdoor | Indoor | Mounting Type | J-Box |
| Current Draw | 5 mA | Operating Temperature | 0°-55°C, 32°-131°F |
| Operating Humidity | 5-95% RH (Non-Condensing) | Wire Connection Type | RJ-45 |
| Engraving Type | Text | Storage Temperature | 23° - 176° F, -5° - 80° C |
