



Dual Slide 3-Speed De-Hummer Fan Control with Single-Pole Dimmer

## Features & Benefits

Tough impact-resistant thermoplastic housing.

Superior heat management: no time wasting break off tabs.

Can be used with patented Snap-In Light Module (sold separately).

Power-failure memory.

Device comes with wired leads.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007236088
Country Of Origin	China	Product Series	Trademaster
Features	Combination, De-Hummer Fan Control, Low-End Trim (Dim Range)	Switch Type	Single Pole, Slider
Number of Switches	2	Application Sector	Residential
Standard	UL Listed	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	109655	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Load Rating	120V 1.6A (FAN MOTOR), 120V 300W (Halogen), 120V 300W (Incandescent)	Operating Cycles	100000
-------------	--	------------------	--------

---

Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
-----------------------	---------------	------------------	-------

---

Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
-----------------	-------------	-----------	---------------

---

Requires Neutral Wire	No	Indoor/Outdoor	Indoor
-----------------------	----	----------------	--------

---

Mounting Type	Wall Box	Wire Connection Type	Flying Leads
---------------	----------	----------------------	--------------

---

Voltage	120 VAC	Load Type	Fan Motor, Incandescent
---------	---------	-----------	-------------------------

---