



Ortronics
Infinium M4 Cassette 12 Fiber, LC, Single-Mode OS2, Type B
Part No. M4LCD12-09C1A1



Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.

Features & Benefits

Method B connectivity: Has flipped polarity and uses key-up to key-up adapters

Fiber port labeling: Provides easier administration

Specifications

General Info

Product Line	Ortronics	UPC Number	662875000945
Country Of Origin	China	Application Sector	Commercial
Standard	TIA-568-C.3	Warranty Type	5-Year
Type	Cassette		

Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Compatibility	HDFP, LM4
------------------------	-----	---------------	-----------

Number of Ports

12

Single/Multimode

Single-Mode

Performance Level/Tier

Infinium Core
