



Ortronics
M4 Cassette, 12 Fiber, LC Duplex, SM OS2, Type B, Far End
Part No. M4LCD12-09C1B1



Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.

Features & Benefits

Fully Compatible with Infinium INFC Enclosures

4 Cassettes Fit into 1U

Front Adapter Housing Colors Follow TIA/EIA-568.3-D Suggested Color Identification Scheme

Each cassette has a data label with insertion loss value for each port

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875000969	Country Of Origin	China
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette

Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Operating Temperature Min	0 °C
Compatibility	HDFM	Number of Ports	12
Simplex/Duplex	Duplex	Operating Temperature Max	70 °C
Return Loss	55 dB	Single/Multimode	Single-Mode
Performance Level/Tier	Infinium Core	Operating Temperature	0°-70°C
Storage Temperature	-40° - 70° C		
