

Infinium M4 Cassettes are part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution can enable industry leading pre-terminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.



Features & Benefits

- Fully Compatible with Infinium INFC Enclosures
- 4 Cassettes Fit into 1U
- Front Adapter Housing Colors Follow TIA/EIA-568.3-D Suggested Color Identification Scheme
- Each cassette has a data label with insertion loss value for each port

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875022152	Country Of Origin	China
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette

Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Fiber Optic Cable Type	OM4	Operating Temperature Min	0 °C
Compatibility	HDFM	Number of Ports	12
Simplex/Duplex	Duplex	Operating Temperature Max	70 °C
Return Loss	55 dB	Single/Multimode	Multimode
Performance Level/Tier	Infinium Ultra	Operating Temperature	0°-70°C
Storage Temperature	-40° - 70° C		