



Ortronics  
**24-FIBER OS2 M4 CASSETTE WITH 24 LC QUAD ADAPTERS TO 2 MPO M- TIER 1**  
Part No. M4LCQ24-09A1A2



Infinium M4 Cassettes are part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution can enable industry leading pre-terminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

## Features & Benefits

High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures : Versatile Installation: Infinium Modular Panel enables mixed media installations

Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber Insertion loss value for each port printed on adhesive data label

## Specifications

### General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875984313	Country Of Origin	Mexico
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette

### Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Fiber Optic Cable Type	OS2	Compatibility	Infinium, M4
Number of Ports	24	Single/Multimode	Single-Mode
Performance Level/Tier	Infinium Core		