



Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.

## Features & Benefits

High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures :

Versatile Installation: Infinium Modular Panel enables mixed media installations

Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber

Insertion loss value for each port printed on adhesive data label

## Specifications

### General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875001270	Country Of Origin	United States
Application Sector	Commercial	Standard	TIA-568-C.3
Warranty Type	5-Year	Type	Cassette

### Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Fiber Optic Cable Type	OS2	Compatibility	Infinium, M4
Number of Ports	24	Single/Multimode	Single-Mode
Performance Level/Tier	Infinium Core		