



Ortronics

**24-FIBER OM4 M4 CASSETTE WITH 6 LC QUAD ADAPTERS TO 3 MPO F- TIER 3- UNIVERSAL POLARITY NON-FLIPPED- AQUA**  
Part No. M4LCQ24-50EE3G1



The 24-fiber OM4 M4 Cassettes are designed to be used with the Infinium HD Enclosures and support MPO to LC Quad adapter 8-fiber connectivity, offering versatile installation and swift deployment. The housing of the cassettes offer additional durability and integrated bend limiting considerations to assure optimum optical performance. The Base 8 configuration of this cassette matches the fiber utilization of most transceivers, providing for 100% fiber utilization. This makes these cassettes a perfect match for Ethernet transmission ranging from 40G to 400G.

## Features & Benefits

High Density: 12 or 24-fiber cassette compatible with Infinium HD M4 Enclosures

Versatile Installation: Infinium Modular Panel enables mixed media installations

Fiber Type: Supports either Single-mode OS2 or Multimode Infinium Ultra fiber

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875026051
Country Of Origin	China	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

### Dimensions

Product Width US	4.24 in
------------------	---------

### Additional Information

RoHS Compliant	Yes
----------------	-----