Ortronics

Clarity CAT6A Modular Patch Cord, 25 ft, White

Part No. MC6A25-09



Clarity 6A modular patch cord, white, 25', Cat6A, 10 Gigabit, four-pair UTP stranded 26 AWG PVC/CM, center tuned with Clarity connecting hardware for optimum installed performance using Ortronics Paralign 2 pair-positioning technology.

Features & Benefits

- Center tuned to Clarity jacks and panels for a more transparent mated union
- Paralign™ 2 plug termination better controls plug performance
- Assembled with premium cordage, 100% factory tested for performance, reliability and long life
- Narrow Paralign plug profile supports use in high density panels and hubs
- Icon compatible – provides additional TIA-606-A designation capabilities

Specifications

General Info

Product Line	Ortronics	UPC Number	662875188209
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	ANSI/TIA 568-C.2	Type	Copper Patch Cord

Dimensions

Product Length US	25.0 FT

Additional Information

RoHS Conformant	Yes	Product Environmental Profile	Yes