



The wire frame and rack unit finger design promotes efficient routing of patch cords between racks. Dual hinged slam latch doors allow easy access during moves, adds and changes. Supplied with four cable management spools to provide slack storage for fiber jumpers and twelve bend limiting clips to protect fiber entering the vertical manager.

## Features & Benefits

- Accepts 180° Bend limiting clips for fiber access
- Bottom support to eliminate sag and step issues
- Clean aesthetic look
- Spring loaded actuator on handles for smooth opening and closing
- Left or right hinge and removable door.
- 2" deeper fingers for higher density networks
- Deeper vertical managers with up to 40% more room
- Strong flexible fingers
- Larger capacity, including longer finger sections

## Specifications

### General Info

|                    |               |               |                   |
|--------------------|---------------|---------------|-------------------|
| Product Line       | Ortronics     | Color         | Black             |
| Finish             | Powder Coat   | UPC Number    | 662875216131      |
| Country Of Origin  | United States | Included      | Mounting Hardware |
| Application Sector | Commercial    | Warranty Type | 5-Year            |
| Type               | Rack          |               |                   |

### Dimensions

|                  |         |                   |          |
|------------------|---------|-------------------|----------|
| Product Width US | 6.45 in | Product Weight US | 52.59 lb |
| Product Depth US | 15.0 in | Product Height US | 77.0 in  |

---

## Additional Information

---

|                |     |                               |     |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

---

## Technical Information

---

|               |           |            |    |
|---------------|-----------|------------|----|
| Compatibility | Mighty Mo | Rack Units | 45 |
|---------------|-----------|------------|----|

---

|                |    |          |          |
|----------------|----|----------|----------|
| Seismic Tested | No | Mounting | Vertical |
|----------------|----|----------|----------|

---