



The wire frame and rack unit finger design promotes efficient routing of patch cords between racks. Dual hinged slam latch doors allow easy access during moves, adds and changes. Supplied with four cable management spools to provide slack storage for fiber jumpers and twelve bend limiting clips to protect fiber entering the vertical manager.

## Features & Benefits

- Accepts 180° Bend limiting clips for fiber access
- Bottom support to eliminate sag and step issues
- Clean aesthetic look
- Spring loaded actuator on handles for smooth opening and closing
- Left or right hinge and removable door.
- 2" deeper fingers for higher density networks
- Deeper vertical managers with up to 40% more room
- Strong flexible fingers
- Larger capacity, including longer finger sections

## Specifications

### General Info

Product Line	Ortronics	Color	White
Finish	Powder Coat	UPC Number	662875218333
Country Of Origin	United States	Included	Mounting Hardware
Application Sector	Commercial	Warranty Type	5-Year
Type	Rack		

### Dimensions

Product Width US	6.5 in	Product Weight US	39.58 lb
Product Depth US	10.25 in	Product Height US	89.0 in

---

## Additional Information

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

## Technical Information

---

Compatibility	Mighty Mo	Rack Units	51
---------------	-----------	------------	----

---

Seismic Tested	No	Mounting	Vertical
----------------	----	----------	----------

---