



The NV-4IC6-DVC utilizes two Aluminum tweeters and a 6.5" dual voice coil Glass Fiber Woofer. This speaker offers a super clean look, and is finished beautifully with their completely rimless, magnetic grills. They also offer quick and secure installation by utilizing three dog legs, instead of the usual four, and includes a unique tweeter bridge that maximizes sound quality, looks great, and serves as a handle to hold the speaker by during installation.

Features & Benefits

| | |
|---|---|
| 8 ohm rated | Beautiful bezeless design and paintable grill for discreet speakers that blend into any décor |
| Grant better at home listening through quality design and materials | Lifetime Warranty |
| Magnetic rimless and paintable grill | Pivoting tweeter |
| Three dog leg design for easy installation | Unique tweeter bridge that also doubles as an installation handle |

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|---------------------------|
| Product Line | Nuvo | Color | Black |
| UPC Number | 701963859000 | Country Of Origin | China |
| Application Sector | Residential | Standard | CE, RoHS, REACH Compliant |

Technical Information

| | | | |
|----------------------|-------|----------|--------|
| Transformer Settings | None | Wattage | 9.06 W |
| Impedance | 8 Ohm | Decibels | 86 dB |