



Nuvo  
**Discontinued - P4300 Professional Series Player, SUB NVP5100NA**  
Part No. NVP4300NA

With a back-lit touch screen for configuration, system status, and the ability to show zone names, the P4300 Professional Series Player (NV-P4300-XX) is the latest generation of Nuvo Players. Providing 110 Watts of power per zone, this single rack-mount unit delivers high fidelity audio to three independent zones. Your music is always in hand with built-in access to streaming services and the ability to play content from networked computers and your iOS and Android devices.



Super efficient Class D amplifiers provide the best quality audio the Player Portfolio has had to date and P4300 has side mounted heat sinks and no fans to allow convenient, single-space rack mounting. Power output remains consistent and can be set to 4, 6 or 8 ohm within the app during setup. All line inputs and line outputs use a combination 3.5mm analog/Toslink connection.

Check out the [Player Portfolio mobile app](#).

Outside North America? Use -EU, -UK or -AU when ordering.

## Features & Benefits

- |  |   |
|--|---|
| 3.5mm combination analog/TOSLINK jacks for line inputs and outputs                       | A single rack-mount unit delivers high fidelity audio to three independent zones                  |
| Backlit touchscreen supports easy setup with visible system status, zone names, and more | Built-in access to streaming services- Spotify, iHeartRadio, TuneIn, Napster, Deezer and SiriusXM |
| Easily play music from networked drives, mobile devices or computers                     | Efficient Class D amplifiers with 110 watts per zone at 8, 6 or 4 ohms                            |
| Side mounted heat sinks and no fans for convenient single-space rack mounting            |   |

## Specifications

### General Info

Product Line	Nuvo	Replaced by Part Number	NVP5100NA
Color	Black	UPC Number	701963859529
Country Of Origin	China	Application Sector	Residential

---

Standard

cTUVus, CE-LVD, FCC CFR Title 47 Part 15  
Subpart B, ICES-003, CISPR13, 55020, C-TICK,  
AS/NZS CISPR13

---