



Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification



Features & Benefits

Up to 72 LC fibers per RU	Available in, LC, SC, ST and blank styles
Made of durable polycarbonate	Zirconia ceramic sleeves for optimal performance
6, 8, 12 & 24 port panels	Color options available

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875593812	Country Of Origin	Mexico
Application Sector	Commercial	Warranty Type	5-Year
Type	Adapter Panel		

Dimensions

Product Width US	5.12 in	Product Depth US	1.15 in
Product Height US	1.19 in		

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Number of Ports	24
Simplex/Duplex	Duplex	Single/Multimode	Single-Mode
Number of Fibers	24 Fibers	Fiber Type	Single-Mode OS2
Form Factor	LC Quad		
