
Cablofil
**Single Hanger Channel**
Part No. P602294



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding, Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Made from 12-gauge strut

Hangers have 9/16'' diameter holes 13/16'' from each end to accept 1/2'' threaded rod

When used with Z-type hold-down clamps, select hanger with flange out dimensions

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Cablofil | Finish | Stainless 316 |
| UPC Number | 800388525542 | Country Of Origin | Mexico |

### Dimensions

| | | | |
|---|---|---|---|
| Product Weight US | 3.67 lb | Product Depth US | 22.0 in |

### Buy American Act Compliance

| | |
|---|---|
| BAA | Yes |