



Cablofil  
LD-6L2I-9112-12 SS304 90 IVR 12"R 12"W  
Part No. P645333



Choose from an extensive selection of metallic ladder tray with a variety of rung and bottom styles to choose from. Finishes include steel, 304L and 316L stainless steel to meet the needs of any application. Rail heights range from 4" to 7" and width sizes are available up to 36".

## Features & Benefits

Includes splice plates

## Specifications

### General Info

Product Line	Cablofil	Finish	Aluminum
UPC Number	800388534735	Country Of Origin	Mexico
Bottom Type	Ladder	Application Sector	Commercial, Industrial
Type	Vertical Other		

### Dimensions

Product Width US	6.0 in	Product Weight US	3.394 lb
Product Height US	4.0 in	Radius	12 in

### Trade Programs

BAA	Yes
-----	-----