



Clarity SNAP™ Terminated Copper Cabling System offers the above-the-standards performance of Clarity® connectivity in a custom terminated cable assembly system that's ready to plug and go. Its innovative modular design combines high performance and installer friendly features with the quick deployment and reliability of a factory terminated and tested cabling system.

Each Clarity SNAP cable assembly includes an identification label, which includes part number, performance level and serialized quality assurance number for future traceability.

## Features & Benefits

- Totally modular cabling system: Dramatically faster deployment of horizontal cabling and port replication
- Factory-installed and tested terminations: Assembled in a controlled factory environment for consistent performance to elevated requirements confirmed by factory testing. Factory tested terminations reduce the time and cost of field testing
- Reduced size of cable ends: Easier cable pulling and directing through pathways and racks
- Clarity® 6A/10G, 6 and 5E performance: Premium performance you've come to rely on from Clarity connectivity, now in a terminated solution
- Variety of options: Solutions tailored to your specific needs
- Increased flexibility for MACs: Reduces total cost of ownership and allows re-use in the future (also reducing waste)

## Specifications

### General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875826705	Country Of Origin	Mexico
Features	Pre-terminated Trunk	Application Sector	Commercial
Warranty Type	5-Year	Type	Patch Cable

### Dimensions

Product Length US	140.0 FT	Cable Length	140 ft
-------------------	----------	--------------	--------

### Technical Information

Operating Temperature Min	-20 °C	Category Performance Rating	Cat6a
Wire Gauge	23 AWG	Storage Humidity	0-100% RH (Non-Condensing)
Plating Specification	50 µ in Gold	Jacket Application	Plenum Rated
Bend Radius	0.94 in	Shielded/Unshielded	Unshielded
Conductor	4-Pair Twisted	Conductor Stranding	Solid

---

Operating Temperature Max	60 °C	Shield Type	F/UTP
Cable Type	Ethernet Patch Cable	Jacket Rating	LSZH
Amperage	0.96 A	Cable Diameter	0.236 in
Wattage	100 W	Operating Temperature	-20°-60°C
Operating Humidity	0-100% RH (Non-Condensing)	Conductor Material	Copper
Voltage	57.0 V		

---