



Pass and Seymour
Medium duty, Long Length, Flexible Eye
Part No. PM0753

Medium-duty, Long length, Flexible eye. Cable Diameter - 0.750-0.990-inch, Mesh Length - 48-inch, Break Strength - 8,100 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 48

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007185614
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Maximum Cable Range	0.75 in	Minimum Cable Range	0.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations