



Pass and Seymour
Medium Duty, Standard Length, Flexible Eye, T-Type
Part No. PM1002

Medium Duty, Standard Length, Flexible Eye, T-Type. Cable Diameter - 1.000-1.490-inch, Mesh Length - 36-inch, Eye Diameter - 5/16-inch, Break Strength - 9,600 lbs.



Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 36: Eye Diameter: 5/16

Specifications

General Info

| | | | |
|--------------------|----------------|--------------|---|
| Product Line | Pass & Seymour | UPC Number | 785007185621 |
| Country Of Origin | Mexico | Construction | Support and Strain Relief Grips, Various Types of Pulling |
| Application Sector | Industrial | Standard | UL/CSA Approval (consult factory) |

Technical Information

| | | | |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 1 in | Minimum Cable Range | 1.49 in |
| Capacity | Various Cable Diameter Ranges | Mounting | Consult the Factory for Mounting Recommendations |