



Pass and Seymour  
Medium Duty, Short Length, Flexible Eye, T-Type  
Part No. PM1501

Medium Duty, Short Length, Flexible Eye, T-Type. Cable Diameter - 1.500-1.990-inch, Mesh Length - 24-inch, Eye Diameter - 7/16-inch, Break Strength - 16,400 lbs.



## Features & Benefits

Medium-duty pulling grips are ideal for overhead and underground pulling applications that require additional durability at an economical price.

Medium-duty pulling grips are hand crafted with single weave strands that graduate to a double weave design for added strength and durability.

Mesh Length: 24: Eye Diameter: 7/16

## Specifications

### General Info

|                    |                |              |   |
|--------------------|----------------|--------------|---|
| Product Line       | Pass & Seymour | UPC Number   | 785007185218  |
| Country Of Origin  | Mexico         | Construction | Various Types of Pulling, Support and Strain Relief Grips |
| Application Sector | Industrial     | Standard     | UL/CSA Approval (consult factory)                         |

### Technical Information

|                     |                               |                     |  |
|---------------------|-------------------------------|---------------------|--|
| Maximum Cable Range | 1.5 in                        | Minimum Cable Range | 1.99 in  |
| Capacity            | Various Cable Diameter Ranges | Mounting            | Consult the Factory for Mounting Recommendations |