



Infinium 384 Offers ultra-high density Mini Duplex Connector (MDC) pass-through adapters which are organized to maximize fiber density while using the flexible and robust MDC connectors. These 1RU panels offer a density of 384 fibers (192 MDC Connectors) in a single unit of rack space. These panels have a front door to provide a clean look and to help protect the delicate cables. The rear support plate comes with two Multi-Use Mounting plates that feature eight HiLOC cradles. For cable management both the front and rear of the panel have several tiedown points to ensure proper routing, protection and a clean look for the fiber cables housed within the panel. The construction of the panel is powder-coated steel and is designed for optimal performance.

## Features & Benefits

**Panel Door:** These panels have a front door to provide a clean look and to help protect the delicate cables

**Cable Management Rear:** The rear support plate includes two Multi-Use Mounting plates with eight HiLOC cradles for secure trunk mounting. It also features 22 tie-down points and 4 rear lip tie-downs for optimal cable management and routing.

Includes Infinium 1U MDC Rack Mount Adapter Panel, Hook & Loop Straps, HiLoc Cradles, Mounting Hardware

**Cable Management Front:** Four individual tie downs provide proper routing and protection of cables. While the front pillars ensure that cables do not pass the side egress point

**Splicing:** The rear support plate also offers compatibility with the FST3-A144 splice tray, enabling ribbon splicing on this panel.

## Specifications

### General Info

Product Line	Ortronics	Color	Magnesium
UPC Number	662875037415	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Warranty Type	5-Year
Type	Patch Panel		

### Dimensions

Product Width US	19.0 in	Product Depth US	17.16 in
Product Height US	1.75 in		

### Technical Information

Compatibility	Infinium	Rack Units	1
---------------	----------	------------	---

---

Connector Type

MDC

---