



Wiremold
Plug-In Outlet Center Unit / 120V/15A/6 O/L /lighted switch/6' cord/Value Grade Surge
Part No. PR610N



Basic surge protection. Six outlets, lighted switch, impact-resistant putty white polymetric housing, 15A. 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug. Maximum surge current 6500 Amps. 11 3/4" x 2 1/4" x 1 1/2 (298mm x 57mm x 38mm). Keyhole mounting.

Features & Benefits

Basic surge protection. Six outlets, lighted switch, impact-resistant putty white polymetric housing, 15A. 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug.

Maximum surge current 6500 Amps. 11 3/4" x 2 1/4" x 1 1/2 (298mm x 57mm x 38mm). Keyhole mounting.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776130072
Country Of Origin	China	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	11.73 in	Product Weight US	1.5 lb
Product Height US	1.5 in	Product Length US	2.24 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E111219	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	6500A

Type of Indicators	Light	Voltage	120.0 V
--------------------	-------	---------	---------
