Pass and Seymour
**Series 16 In-Line Connectors, Yellow**
Part No. PS40FBY



400A 600V, Cable Size 2/0 - 4/0, Female Cam-Type Plug, Yellow

## Features & Benefits

- Thermoplastic elastomer housing for outstanding impact and chemical resistance
- Exceptional seal for maintaining NEMA Type 3R and 4 integrity
- Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product
- Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity
- Heavy-duty hex set screws allow greater termination torque
- Copper wire provides quality strain relief
- Copper shim bundles wire strands to reduce "splaying."

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | Mexico | Application Sector | Commercial/Industrial |
| Standard | UL, cCSAus | | |

### Dimensions

| | |
|---|---|
| Product Length US | 6.8 in |

### Technical Information

| | | | |
|---|---|---|---|
| Amperage | 400 A | Number of Poles | Single Pole |
| Wire Size | 2/0 - 4/0 | Voltage | 600 V |

| | |
|---|---|
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4 |