



Pass and Seymour
Discontinued - PlugTail® 15A 125V Commercial Spec-Grade USB Type A/C Outlet, Black
Part No. PTTR15ACUSBBK



PlugTail® Commercial Specification Grade USB Charging Receptacles provide the convenience of mobile charging without the need for a bulky AC adapter. This device is a perfect match for the constant needs of today's mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices - one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides all power needed for charging mobile phones and tablets. The PlugTail® termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations. For detailed PlugTail® information, visit our PlugTail® Headquarters. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

AC receptacles are tamper resistant as standard : patented shutter system prevents improper insertion of foreign objects

Triple-wipe, brass line contacts for 15A commercial applications

Zinc-plated steel for corrosion resistance

Stainless steel auto-ground clips assure positive ground

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Plated steel wrap strap design for maximum durability and corrosion resistance.

Multiple color options available

5Vdc Type-C USB port to charge USB Type-C compatible mobile devices

Available in 15 & 20A, Specification Grade and Hospital Grade configurations

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	PTTR15ACUSBBK
Color	Black	UPC Number	785007110081
Country Of Origin	China	Number of Receptacles	2
Features	USB-A Charging, USB-C Charging	Outlet Type	USB-Charging
Application Sector	Commercial	Standard	FEDSPEC
Type	Outlet		

Dimensions

Product Width US 1.693 in

Product Depth US

1.45 in

Product Height US 2.677 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

USB Amperage 3.1 A

Number of USBs

2

USB Power Output 15 W

Amperage

15 A

Number of Poles Double Pole

Indoor/Outdoor

Indoor
