



Vantage
Lighting Relay Module (DIN)
Part No. RS8-L-DIN



The DIN Lighting Relay Station is designed to control non-dimmable lighting and switchable loads and provides eight isolated latching relay outputs. The RS8-L-DIN accepts voltage from 0 to 277 Volts and up to 10 Amps at each load. The relays are single-pole, single throw, offering a set of eight latching contacts. This station may also be used as a low-voltage relay station. Actuator buttons allow the connected relays to be manually toggled. Relays latch in place retaining its last state in case of a power interrupt.

Features & Benefits

All relays are rated for lighting type loads

Provides a single integration point for up to eight relay channels

Allows effortless control of devices such as lighting loads, draperies, pumps, garage doors, lifts, screens, pool covers, sprinklers, security systems, and much more

Specifications

General Info

Product Line	Vantage	UPC Number	804428050704
Country Of Origin	China	Application Sector	Residential
Type	Accessory		

Dimensions

Product Width US	15.0 in	Product Weight US	22.42 lb
Product Height US	11.5 in	Product Length US	18.5 in

Technical Information

Seismic Tested	No
----------------	----