



This MSA Compliant SFP+ transceiver provides 10GBase-SR throughput up to 300m over multi-mode fiber (MMF) at a wavelength of 850nm using a LC connector. It is built to MSA standards and is uniquely serialized and data-traffic and application tested to ensure that they will integrate into your network seamlessly. It is built to meet or exceed the specifications of MSA Compliant, as well as to comply with MSA (Multi-Source Agreement) standards to ensure seamless network integration. All Legrand transceivers are Trade Agreements Act (TAA) compliant.

Features & Benefits

Supports data rates up to 10Gbps	SFP+ transceiver module
LC ports designed for use with Multimode Fiber	850nm wavelength signaling
Supports up to 300 meters of cabling	

Specifications

General Info

Product Line	Legrand	Color	Silver
UPC Number	757120668121	Country Of Origin	United States
Application Sector	Commercial/Industrial	Type	Active Optical Cable

Trade Programs

TAA Compliant	Yes
---------------	-----

Additional Information

RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
----------------	-----	---	-----