



**Wiremold**  
**Plug-In Outlet Center Unit / 120V/15A/7 O/L /lighted switch/6' cord/Value Grade Surge**  
Part No. SR10N



Basic surge protection. Seven outlets, one spaced for transformers, lighted switch, impact-resistant putty white polymeric housing, 15A. 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug. Maximum surge current 6500 Amps. 13 1/4" x 2 1/2" x 1 9/16 (337mm x 64mm x 40mm). Keyhole mounting.

## Features & Benefits

Basic surge protection. Seven outlets, one spaced for transformers, lighted switch, impact-resistant putty white polymeric housing, 15A. 6' (1.8m) 14/3 SJT putty white cord with NEMA5-15 plug.

Maximum surge current 6500 Amps. 13 1/4" x 2 1/2" x 1 9/16 (337mm x 64mm x 40mm). Keyhole mounting.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776103090
Country Of Origin	China	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

### Dimensions

Product Width US	13.27 in	Product Weight US	1.7 lb
Product Height US	1.57 in	Product Length US	2.52 in

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E111219	cULus Listed	Yes
---------------------	---------	--------------	-----

### Additional Information

RoHS Compliant	Yes
----------------	-----

### Technical Information

Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	6500A

---

Type of Indicators	Light	Voltage	120.0 V
--------------------	-------	---------	---------

---