



Pass and Seymour  
TradeMaster® 0-10V Fluorescent/LED Single Pole/3-Way Toggle Slide Dimmer, Preset, Brown  
Part No. TSD4FBL3P



Toggle Slide Dimmer Color Change Kit

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Gloss	UPC Number	785007216943
Country Of Origin	China	Product Series	Trademaster
Features	Color Change Kit, Low-End Trim (Dim Range)	Switch Type	3-Way, Single Pole, Slider, Toggle
Number of Switches	1	Application Sector	Commercial, Hospitality, Residential
Warranty Type	Limited Lifetime Warranty		

### Dimensions

Product Width US	1.73 in	Product Depth US	1.4 in
Product Height US	4.19 in		

### Technical Information

Preset	Yes	Load Rating	120V 10A (Fluorescent), 120V 10A (LED), 277V 5A (Fluorescent), 277V 5A (LED)
Dimming Compatibility	0-10 V	Frequency Rating	60 Hz
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Voltage	120/277 VAC	Load Type	Fluorescent, LED

