



Pass and Seymour
4-in Round Outdoor Cluster Cover, Bronze
Part No. WPRB11BR

Weatherproof 4-inch Round Outdoor Cluster Cover, Blank 1 Hole
1/2-in With Gasket and Screws



Features & Benefits

Wide range of rectangular and round covers.

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

Kits available combining fixtures, lamp covers, and accessories.

Specifications

General Info

Product Line	Pass & Seymour	Color	Bronze
Finish	Metallic	UPC Number	785007117073
Country Of Origin	India	Wall Plate Type	Custom
Application Sector	Industrial	Standard	UL Listed
Warranty Type	1-Year Limited Warranty	Type	Weatherproof Cover

Dimensions

Product Width US	4.625 in	Product Depth US	1.0 in
Product Height US	4.625 in		

Technical Information

Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
----------------	--------	---------------	-------------