Pass and Seymour

Weather-Resistant Heavy Duty Spec Grade Receptacles, Back and Side Wire, 20A, 250V, White

Part No. WR5862W



Weather-Resistant Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 20A 250V

Features & Benefits

- Auto-ground clip assures positive ground.
- Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.
- Tri-drive brass terminal screws.
- Two back wire holes for more wiring flexibility.
- UV-resistant nylon face for longer life under adverse environmental conditions.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- For covering patents, see www.legrand.us/patents.
- WR marking on face as required by UL Standard.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Internal screw-pressure-plate back and side wire capability.
- Heavy-duty, brass strap for added strength and ground conductivity.
- Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Commercial	Standard	UL 498

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes

Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	250 V