Pass and Seymour

# Discontinued - Hospital-Grade USB Charger with Tamper-Resistant 15A Duplex Receptacles, White

Part No. TR8200HUSBW

## Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices

AC receptacles available in 15 and 20 Amp, 125V

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

Stainless steel auto-ground clips assure positive ground.

For covering patents, see www.legrand.us/patents.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Replaced by Part Number | TR15HUSBAC6W |
| Color | White | UPC Number | 785007031799 |
| Country Of Origin | China | | |

### Listing Agencies / 3rd Party Agencies

| | |
|---|---|
| cULus Listed | Yes |

### Additional Information

| | |
|---|---|
| Product Environmental Profile | Yes |

### Technical Information

| | | | |
|---|---|---|---|
| Is Tamper-Resistant | Yes | USB Amperage | 3.1 A |
| Number of USBs | 2 | USB Power Output | 15 W |
| Amperage | 15 A | | |