Pass and Seymour

Discontinued - SW 3W 20A 347V DECOR LT ALMOND

Part No. 2623347LA

Specification Grade Decorator Switch 3-way, Back and Side-Wire, Decorator Switch, 20A, 347V

Features & Benefits

Impact-resistant polycarb back body and frame.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Integral auto-ground clip for positive ground to metal boxes.

Tri-drive ground, terminal, and mounting screws.

All terminal screws backed out, ready-to-install.

For covering patents, see

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007260274
Country Of Origin	Mexico	Features	Decorator Style
Switch Type	Paddle	Application Sector	Commercial, Residential
Type	Decorator, Switch		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Technical Information

Operating Temperature Min	-4 °F	Contact Rating	20amp, 347vac
Operating Temperature Max	140 °F	Amperage	20 A
Number of Poles	3-Way	Wire Size	#14 - #10 AWG
Indoor/Outdoor	Indoor	Mounting Type	Box
Operating Temperature	-4°-140°F (-20°-60°C)	Voltage	347.0 V