OPTIONS UP





FEATURES & BENEFITS

Constant memory returns lights to previous levels after a power failure

Convenient operation - combines on/off toggle switch with separate slider for dimming control

Screw-pressure-plate backwire terminals save time, space and money



New aesthetically pleasing ergonomic design allows for easier operation

Adjustment dial allows users to adjust the bottom of the dimming range for a wide range of CFL and LED bulbs

Interchangeable face plates available in seven colors (TSDKIT*; sold separately)









TSDCI 303P

PRESS TABS

- Preset, Single Pole and 3-Way operation.
- Compatible with CFL/LED dimmable bulbs (with the exception of 0-10V LED drivers).



LED



CFL



MLV



LED



INCANDESCENT



FAN SPEED CONTROL

PRODUCT INFORMATION

PART NUMBER	DESCRIPTION	COLOR	RATINGS	
TSD703PTUTC	Tru-Universal®	Three interchangeable face colors; White, Light Almond, Ivory	700W Incandescent, Halogen & ELV; 500VA MLV; 450W CFL/LED; 5.5A EFL	
TSD703PTU*	Single Pole/3-Way, Preset	White, Light Almond, Ivory, Brown, Black, Red, Gray		
TSDCL303PTC	CFL/LED	Three interchangeable face colors; White, Light Almond, Ivory	300W CFL/LED; 700W Incandescent & Halogen	
TSDCL303P*	Single Pole/3-Way, Preset	White, Light Almond, Ivory, Brown, Black, Red, Gray		
TSD703PTC	Incandescent	Three interchangeable face colors; White, Light Almond, Ivory	FOOM!	
TSD703P*	Single Pole/3-Way, Preset	White, Light Almond, Ivory, Brown, Black, Red, Gray	700W Incandescent	
TSD1103PTC	Incandescent	Three interchangeable face colors; White, Light Almond, Ivory	1100W Incandescent	
TSD1103P*	Single Pole/3-Way, Preset	White, Light Almond, Ivory, Brown, Black, Red, Gray		
TSDLV703PTC	Magnetic Low Voltage Single Pole/3-Way, Preset	Three interchangeable face colors; White, Light Almond, Ivory	700\/A M	
TSDLV703P*		White, Light Almond, Ivory, Brown, Black, Red, Gray	700VA Magnetic Low Voltage	
TSDLV1103PTC	Magnetic Low Voltage	Three interchangeable face colors; White, Light Almond, Ivory	1100\/\ \\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	
TSDLV1103P*	Single Pole/3-Way, Preset	White, Light Almond, Ivory, Brown, Black, Red, Gray	1100VA Magnetic Low Voltage	
TSDFB83PTC	Fluorescent	Three interchangeable face colors; White, Light Almond, Ivory	OA Florence A Diegono	
TSDFB83P*	Single Pole/3-Way, Preset	White, Light Almond, Ivory, Brown, Black, Red, Gray	8A Fluorescent Dimmers	
TSD4FBL3PTC	Fluorescent	Three interchangeable face colors; White, Light Almond, Ivory	120V 10A/277V 5A LED (0-10V, 4 wire,	
TSD4FBL3P*	Single Pole/3-Way, Preset	White, Light Almond, Ivory, Brown, Black, Red, Gray	fluorescent dimming of drivers and ballasts)	
TSDDH163PTC	Fan Speed Control	Three interchangeable face colors; White, Light Almond, Ivory	1 / A Fan Chand Cantas	
TSDDH163P*	Single Pole/3-Way, Preset	White, Light Almond, Ivory, Brown, Black, Red, Gray	1.6A Fan Speed Control	
TSDSSL7APTC	SSL7A Compliant	Three interchangeable face colors; White, Light Almond, Ivory	300W CFL/LED; 700W Incandescent	
TSDSSL7AP*	Single Pole/3-Way, Preset	White, Light Almond, Ivory, Brown, Black, Red, Gray	& Halogen	

PART NUMBER	DESCRIPTION	COLOR
TSDKIT*	Interchangeable Face Plate	White, Light Almond, Ivory, Brown, Black, Red, Gray










COLOR DESIGNATION				
W	White			
LA	Light Almond			
1	lvory			
-	Brown			
вк	Black			
RED	Red			
GRY	Gray			



designed to be better.



Electrical Wiring Systems

60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us

Canada 1.800.723.5175; 905.738.9195 www.legrand.ca

Costa Rica +506.298.56.04; +506.239.71.13 www.legrand.cr

