


RESIDENTIAL DIMMERS & FAN SPEED CONTROLS

radiant™ Incandescent and Low Voltage Dimmers



RH703PW

RH1103PLA

RHLV703PW

RHLV1103PLA

Features

- Part of the radiant™ collection.
- Convenient operation – combines ON/OFF paddle switch with separate slider for dimming control.
- White LED glows when OFF to make dimmer easy to find in the dark.
- Constant memory returns lights to previous level after a power failure.
- Higher ratings.

- Single pole and 3-way operation.
- Works with standard 3-way switches and wiring.
- Screw-pressure-plate back wire terminals save time, space and money.

RH703P, RHLV703P

- No de-rating.
- No fins to break.

Interchangeable Face Versions

- Package comes with three face colors – Ivory, White, Light Almond (TC).
- White-only option also available.
- Interchangeable faces available in nine colors (sold separately, see below).

CATALOG NUMBER	DESCRIPTION	RATINGS	COLOR
INCANDESCENT SINGLE POLE/3-WAY DIMMERS*			
RH703PW	Incandescent Preset, Single Pole and 3-Way	120V, 700W	White
RH1103PW	Incandescent Preset, Single Pole and 3-Way	120V, 1100W	White
INTERCHANGEABLE FACE INCANDESCENT SINGLE POLE/3-WAY DIMMERS			
RH703PTC	Incandescent Preset, Single Pole and 3-Way Three Interchangeable Face Colors	120V, 700W	Ivory/White/Light Almond
RH1103PTC	Incandescent Preset, Single Pole and 3-Way Three Interchangeable Face Colors	120V, 1100W	Ivory/White/Light Almond
MAGNETIC LOW VOLTAGE PRESET, SINGLE POLE/3-WAY			
RHLV703PTC	Preset, Single Pole/3-Way Three Interchangeable Face Colors	120V, 700VA	Ivory/White/Light Almond
RHLV703PW	Preset, Single Pole/3-Way		White
RHLV1103PTC	Preset, Single Pole/3-Way Three Interchangeable Face Colors	120V, 1100VA	Ivory/White/Light Almond
RHLV1103PW	Preset, Single Pole/3-Way		White
INTERCHANGEABLE FACE COVERS†			
RHKITI RHKITW RHKIT RHKITGRY RHKITBK RHKITLA RHKITAB RHKITDB RHKITNI	Interchangeable Face		Ivory White Brown Gray Black Light Almond Antique Brass Dark Bronze Nickel

*Available in VisionPak™ packaging, add "CCV6" to Catalog Number. Example: RH1103PWCCV6.

†Available in VisionPak™ packaging, add "BPCCV6" to Catalog Number. Example: RHKITIBPCCV6.