Pass and Seymour

# 15A, 250V Watertight Duplex Receptacle, Yellow

Part No. 60W49DPLX

Straight Blade Watertight Duplex Receptacle, 15amp 250volt, NEMA Configuration 6-15, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

## Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Yellow |
| UPC Number | 785007033151 | Country Of Origin | United States |
| Application Sector | Commercial | Standard | CSA Listed, FSUL, UL Listed |

### Technical Information

| | | | |
|---|---|---|---|
| Phase | Single | Connection | Cable |
| Number of Wires | 3 | Amperage | 15 A |
| Number of Poles | Double Pole | Wire Size | 18 - 12 AWG |

| | |
|---|---|
| Environmental Conditions | Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature -40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized |