


---

## RADIANT® WIRELESS CHARGER, BLACK

RWC826USBBKCCV2 | [radiant](#)



---

### FEATURES & BENEFITS

The radiant® Wireless Charger instantly provides a convenient, clutter-free charging station, perfect for clearing space on counters and nightstands. It works with Qi-enabled phones, and includes two traditional outlets and a USB port to offer additional power options. Featuring a clean, classic aesthetic the Wireless Chargers include screwless, decorative wall plates, and easily replace standard single-gang outlets using the existing electrical wiring.

For more information on phone compatibility and Qi wireless charging: Click [here](#).

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

- Instantly provides a clutter-free space to charge your phone.
- Replaces any existing single gang outlet for easy installation.
- 3.1A to power any cell phone, tablet or USB device.
- Perfect for new construction or remodel; no need for special wiring.
- Qi certified, assuring a safe, reliable wireless charging experience.
- The radiant® collection offers a consistent look across all switches, dimmers, outlets, and home automation controls
- Includes tamper resistant duplex receptacle with a USB port
- Qi Compatible Smartphone models include: Apple iPhone 8, iPhone 8 Plus, iPhone XR, iPhone XS, iPhone XS Max, iPhone 11, iPhone 11 Pro, iPhone 11 Pro Max; Samsung Galaxy Fold, Galaxy Note 8, Galaxy Note 9, Galaxy Note 10, Galaxy Note 10+ 5G, Galaxy S7, Galaxy S7 Edge, Galaxy S7 Active, Galaxy S8, Galaxy S8 Active, Galaxy S8 Plus, Galaxy S9, Galaxy S9 Plus, Galaxy S10, Galaxy S10e, Galaxy S10 Plus, Galaxy S10 5G, Galaxy S20, Galaxy S20 Plus, Galaxy S20 Ultra 5G, Galaxy Z Flip; Nokia 8 Sirocco; Sony Xperia XZ2, Xperia XZ3, Xperia 1 II; Google Pixel 3, Pixel 3 XL, Pixel 4, Pixel 4 XL; LG V30, LG V35, LG V40, LG V50.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black

Special Features: 3.1 Amps of total charging capacity

## LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: CSA C22.2 No. 42-10, No. 42.1, No. 223

CSA Standard: Yes

CUL Listing No: UL498; UL1310; UL514D

UL Standard: Yes Qi: WPC Qi Registered, Power Class 0 Transmitter, Qi ID: 2092

## DIMENSIONS

Depth (US): 2.42"

Height (US): 4.92"

Width (US): 6.05"

## TECHNICAL INFORMATION

Amps: 15

NEMA Configuration Number: 5-15R

## COUNTRY OF ORIGIN

Country Of Origin: CHINA