



## 6AT THREE HOUR FIRE RATED, UNWIRED EVOLUTION™ RECESSED POKE-THRU DEVICE, SURFACE STYLE COVER, BRUSHED ALUMINUM

6ATC2AA3H | [Wiremold](#)

### FEATURES & BENEFITS

The Industry's first 3 hour fire rated recessed Poke Thru is here. Designed for retrofit and new construction, Evolution Series 6" Recessed Poke-Thru Devices provide convenient access to power, communications and audio/video services recessed below floor level - providing maximum device protection. With 3 gangs of capacity, you can configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel and multiple powder-coated finishes designed to match any space. Evolution Series 6" Poke-Thru Devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.

- **Recessed devices:** All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.
- **Multiple preassembled options:** Available in unwired, prewired, and prewired A/V options to save you time on the jobsite
- **"Step-on-it" installation:** Quick and easy installation without the need for additional fasteners or a second installer.
- **Unique cover design:** The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.
- **Multiple finishes:** Evolution Series Poke-Thru Devices are available in multiple finishes: (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AA) brushed aluminum, (SB) satin brass and (SN) satin nickel to seamlessly match your environment.
- **Ideal for high foot traffic environments:** Satin brass, satin nickel and brushed aluminum finishes offer a more durable, high-end look with a tougher clear powder coat.
- **Surface style cover assemblies:** A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete or terrazzo.
- **Open system for expanded compatibility:** Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.
- **Plug load control up to 30 feet:** Tested with Pass & Seymour® Wireless RF Receptacles to control plug loads up to a distance of 30 feet when the cover is closed.
- **3 hour fire rating:** Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 3 hours, the longest of its type.
- **Meets ADA accessibility guidelines:** Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5, which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.
- **UL Listed and UL Fire Classified to U.S. and Canadian safety standards:** UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

## SPECIFICATIONS

### GENERAL INFO

Color: Brushed Aluminum

### CONSTRUCTION INFORMATION

Material 1: Aluminum, Steel, Plastic

### DIMENSIONS

Diameter (US): 7-1/4 in

Height (US): 17-3/4 in

Hole Size: 6"

### TECHNICAL INFORMATION

Material: Aluminum, Steel, Plastic

### COUNTRY OF ORIGIN

Country Of Origin: UNITED STATES OF AMERICA