



Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, **adorne®** and **radiant®** with Netatmo leverage leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart switches, dimmers and outlets to build a solution that perfectly fits a home's unique space and needs. Create and edit lighting scenes in the app (total 8 per system, including Home/Away and Wake/Sleep). Then, use this Pocket Remote Control to control four lighting scenes with a single touch. Add to a key ring or stash in the car's console for one-touch control on the go. Made exclusively for use with the **adorne®** and **radiant®** with Netatmo Smart Lighting solutions.

Features & Benefits

Smart Gateway REQUIRED

Enjoy one-touch control of four lighting scenes (not including Home/Away and Wake/Sleep). Easily create and manage scenes from your smartphone or tablet using the Legrand Home + Control app

Offers long-lasting, battery-powered one-touch scene control on the go. Add to a key ring for easy access as you leave/return, or use around the home for setting the atmosphere even when your phone is out of reach

Part of the **adorne** and **radiant** with Netatmo solutions, which flexibly fit a home's unique needs with a variety of supported smart switches, dimmers and outlets (including wireless switches and dimmers)

Must be used in conjunction with installed Smart Switches, Dimmers and/or Outlets with Netatmo

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems

Features ultra-reliable performance through a robust and dedicated mesh-network

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	Country Of Origin	France
Features	Wireless	Works With	Amazon Alexa, Apple Home Kit, Google Assistant
Application Sector	Residential/Commercial	Standard	IP 20, IK 02, RoHS, FCC, IC, IEC

Warranty Type	2-Year Limited Warranty	Type	Switch
---------------	-------------------------	------	--------

Listing Agencies / 3rd Party Agencies

IEC	Yes	FCC Compliant	Yes
-----	-----	---------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Frequency Rating	2.4 to 2.4835 GHz	Connection	Wireless
------------------	-------------------	------------	----------

Power Consumption	< 100 m:WATTS	Operating Temperature	41°-113°F
-------------------	---------------	-----------------------	-----------

Environmental Conditions	85% (relative humidity, non-condensing)	Storage Temperature	32° - 113° F
--------------------------	---	---------------------	--------------
