Wiremold

AV3 Flush A/V Assembled Poke-Thru Assembly, Black

Part No. AV3ATCBK

A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground. Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS). Aluminum and brass flanges standard with black cover. Aluminum flange also available with an aluminum colored nonmetallic cover (AA). Brass flange also available with brass colored nonmetallic cover (AB). Includes one adpater to accept Legrand AVIP or Extron Electronics MAAP mini architectural adapter plates, Wiremold Open System adapters, and Ortronics TracJack and Series II mounting adapters. Modular Jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. AV3 Series Poke-Thru Devices require a 4inch (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

Features & Benefits

- A/V device includes one prewired 20A duplex receptacle which can be wired as a standard receptacle or isolated ground
- Finish flange available in gray (GY), black (BK), ivory (VY), brushed aluminum (AL) and brass finish (BS)
- Aluminum and brass flanges standard with black cover
- Aluminum flange also available with an aluminum colored nonmetallic cover (AA)
- Brass flange also available with brass colored nonmetallic cover (AB)
- Modular Jacks sold separately
- Modular Jacks sold separately
- NOTE: Assembled with scrub water gasket
- For use on tile or carpet floors
- AV3 Series Poke-Thru Devices require a 4inch (102mm) diameter hole
- Not designed to work with bare concrete or terrazzo
- For use on tile or carpet floors

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786564015598	Country Of Origin	Mexico
Number of Knockouts	2	Application Sector	Commercial
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21 & 300.22(C) & 314 of NEC.	Type	Poke-Thru

Dimensions

Product Width US	8.25 in	Product Weight US	4.96 lb
Product Volume US	1157.06 cu in	Product Depth US	17.0 in
Product Height US	8.25 in	Cubic Capacity	24.5 in^3
Core Hole Size	4 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes

Buy American Act Compliance

NAFTA	Yes

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes

Technical Information

Number of Outlets	2