Pass and Seymour

# 20A NEMA L520 Single Receptacle, Yellow, Corrosion-Resistant

Part No. CRL520R

Turnlok® Receptacle 3-Wire 20A 125V Corrosion Resistant

## Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Yellow |
| UPC Number | 785007252071 | Country Of Origin | Mexico |
| Application Sector | Industrial | Standard | UL Listed |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.61 in | Product Depth US | 1.19 in |
| Product Height US | 2.29 in | | |

## Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | 140596 | cULus Listed | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Phase | Three | Number of Wires | 3 |
| Amperage | 20 A | Number of Poles | Double Pole |