Pass and Seymour

Tamper-Resistant Floor Box Assembly - Two Gang for Wood Sub-Floors, Brass

Part No. FB2TRDRKS4B

Tamper-Resistant Floor Box Assembly, Dual-voltage. Two #8 duplex openings, Four threaded screw plugs. Includes 3232 15A, 125A tamper-resistant duplex receptacle, Cat5E Jack, F-connector, Ten Blanks and a low-voltage dider. Brass. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Meets UL514(c) and NEC 314.27(c) requirements including scrub water for tile floors.
- Large box flange rests on finished floor -- no adjustments needed.
- Extra-deep design leaves plenty of wiring room.
- Rugged diecast cover plates with durable nickel or brass finish.
- Scrub water compliant without caulking, supplied with foam gasket and O-ring-equipped plugs.
- Swing brackets mounting, great for tile floors -- eliminates drilling for mounting screws.
- Includes 15 Amp, 125 Volt tamper-resistant duplex receptacle, low-voltage divider, Cat 5e jack, F-connector, and blanks.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
UPC Number	785007108743	Country Of Origin	Mexico
Construction	Wood Floor	Application Sector	Residential/Commercial
Standard	UL Listed		

Dimensions

Cubic Capacity	42.5 in^3

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Technical Information

Is Tamper-Resistant	Yes	Number of Outlets	2