Pass and Seymour

Flexcor® Support Grips Standard Duty, Closed Mesh, Offset Eye Grips, Cable Diameter 0.75 - 0.99 in.

Part No. FC075OF

FC075OF: Standard Duty, Closed Mesh, Offset Eye Grips, Cable Diameter 0.75 - 0.99 inches, Bale Length 4-in, Mesh Length 14-in, Break Strength 960 lbs.

Features & Benefits

Closed mesh support grips are used when the end of the cable is accessible.

Vertical runs of no more than 100 ft.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Bale Length: 4: Mesh Length: 14

Standard duty closed mesh support grips are designed for loads up to 600 lbs.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

Product Family / Series / Group	Flexcor	Product Line	Pass & Seymour
UPC Number	785007980356	Country Of Origin	Mexico
Product Type	Cord Grip	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Dimensions

Product Width US	0.99 in	Product Length US	13.0 in
Mesh Length	13 in	Cable Diameter Range	0.740-0.990 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507

Technical Information

Mesh Type	Closed	Approximate Break Strength	1000 lb
Maximum Cable Range	0.75 in	Eye Style	Offset
Minimum Cable Range	0.99 in	Capacity	Various Cable Diameter Ranges

Indoor/Outdoor	Both	Mounting	Consult the Factory for Mounting Recommendations