



GFCI receptacles from the radiant Registered Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Maximize safety, in style, with GFCI protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

## Features & Benefits

- Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device
- Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected
- Replaces any standard receptacle with ease, in as little as 10 minutes
- More color options available to fit any style, including finishes to match current hardware and lighting trends
- Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced
- Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly
- Features durable, high-impact resistant thermoplastic construction
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Satin	UPC Number	785007135480
Country Of Origin	China	Number of Receptacles	2
Features	Self-Test	Outlet Type	GFCI
Application Sector	Commercial, Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	1-Year Limited Warranty		

### Dimensions

---

Product Width US	1.73 in	Product Depth US	1.25 in
------------------	---------	------------------	---------

---

Product Height US	4.2 in
-------------------	--------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E42190	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Connection Location	Back and Side	Number of Wires	3
---------------------	---------------	-----------------	---

---

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Indoor/Outdoor	Indoor
-----------------	-------------	----------------	--------

---

NEMA Configuration Code	5-15R	Mounting Type	Box
-------------------------	-------	---------------	-----

---

Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	125.0 V
----------------------	---	---------	---------

---

Environmental Conditions	95% Humidity, UL 94 V2
--------------------------	------------------------

---