Pass and Seymour

Turnlok® Duplex Receptacle 3-Wire 15A 125V Isolated Ground, Orange

Part No. IG4700

Turnlok® Duplex Receptacle 3-Wire 15A 125V Isolated Ground

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Side and external screw-pressure-plate backwire capability. Accepts #14-#10 AWG.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Finish	Matte	Country Of Origin	Mexico
Receptacle Type	Locking	Number of Receptacles	2
Application Sector	Industrial	Standard	UL 498
Type	Isolated Ground		

Dimensions

Product Width US	1.5 in	Product Depth US	4.03 in
Product Height US	1.2 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
CSA File Number	16063		

Technical Information

Phase	3	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	18 AWG	Voltage	125.0 V