



radiant Collection  
**radiant® Tamper-Resistant 15A Simplex Self-Test GFCI Receptacles with SafeLock® Protection, Brown**  
Part No. 1597TRSGL



Perfect for providing dedicated power and reliable ground-fault protection, the simplex 15A GFCI features a single, tamper-resistant outlet and self-tests automatically every three seconds for electrical safety you can trust. Meeting the National Electrical Code requirements for ground fault protection in the home, GFCI wall outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. Maximize safety, in style, with GFCI plug protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

- Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected

Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection
- Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced

Includes green LED illuminated power indication to confirm the receptacle is energized

Replaces a traditional outlet easily, in as little as 10 minutes

More color options available to fit any style, including finishes to match current hardware and lighting trends

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007381467
Country Of Origin	China	Outlet Type	GFCI, Self-Test, Tamper-Resistant
Application Sector	Commercial, Residential	Standard	RoHS, cULus
Warranty Type	1-Year from Day of Sale	Type	GFCI, Tamper-Resistant

Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
------------------	---------	------------------	---------

Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
RoHS Compliant	Yes	Product Has Potential to Contribute to LEED	Yes
Technical Information			
Seismic Tested	No	Is Tamper-Resistant	Yes
Amperage	15 A	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Wattage	1875 W