Pass and Seymour
**30A NEMA L530 Single Receptacle, Blue**
Part No. L530RBL

Turnlok® Receptacle Single 3-Wire 30A 125A,

## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Blue |
| Country Of Origin | Mexico | Application Sector | Industrial |
| Standard | UL Listed | | |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.61 in | Product Depth US | 1.28 in |
| Product Height US | 2.37 in | | |

### Listing Agencies / 3rd Party Agencies

| | |
|---|---|
| cULus Listed | Yes |

## Additional Information

| | |
|---|---|
| Product Environmental Profile | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Phase | 3 | Number of Wires | 3 |
| Amperage | 30 A | Number of Poles | Double Pole |
| Voltage | 125.0 V | | |